

CARSON®

LumiLoupe™ Plus

17.5x Focusable Loupe



LO-15

Congratulations on selecting your new Focusable Loupe! In order to achieve optimum performance, please follow instructions for proper use and care.

PRODUCT SPECIFICATION:

Magnification:	17.5x
Weight:	0.08 lbs
Dimensions:	2.3" x 2.3" x 1.4"

USING LOUPE:

1. Place viewing object on a flat surface like a table and place loupe over it.
2. For best results, your eye(s) should be reasonably close to loupe.
3. To focus, twist black ring until viewing object is clear.

CARE:

Clean using microfiber lens cloth. Do not use any abrasives, chemical cleaners, or solvents.

Customer Service:

If you experience any difficulties, please contact us and we will be happy to help you.



✉ info@carson.com



✉ uksupport@carson.com



✉ eusupport@carson.com

For warranty information, visit www.carson.com/warranty

www.carson.com

Carson Optical 2070 5th Avenue, Ronkonkoma, NY 11779 | Tel: 631-963-5000