

# CARSON®

# MR-25

## MagniRead™

### 1.5x Magnifier Bar

Congratulations on selecting your new MagniRead! In order to achieve optimum performance, please follow instructions for proper use and care.



### PRODUCT SPECIFICATION

Magnification:	1.5x
Weight:	0.09 lbs
Dimensions:	0.9" x 0.6" x 6.3"

### USING THE MAGNIFIER

Hold magnifier by handle. Start with magnifier flat on page and view text or numbers through yellow highlighted area.

**For Best Results:**

- Depending on your vision, you may need to raise magnifier slightly until text is clear.

### CARE

Clean using microfiber lens cloth. Do not use any abrasives, chemical cleaners, or solvents.

#### Customer Service:

If you experience any difficulties, please contact us and we will be happy to help you.



✉ info@carson.com



✉ uksupport@carson.com



✉ eusupport@carson.com

For warranty information, visit [www.carson.com/warranty](http://www.carson.com/warranty)

[www.carson.com](http://www.carson.com)

Carson Optical 2070 5th Avenue, Ronkonkoma, NY 11779 | Tel: 631-963-5000