

# CARSON®

## LumiLoupe™

### 7x Stand Magnifier



# LL-77

Congratulations on selecting your new LumiLoupe Stand Magnifier! In order to achieve optimum performance, please follow instructions for proper use and care.

#### PRODUCT SPECIFICATION:

Magnification:	7x
Weight:	0.26 lbs
Dimensions:	3.0" x 3.0" x 2.5"

#### USING LOUPE:

1. Place loupe over viewing object.
2. Your eye(s) should be reasonably close to loupe.
3. It's best to start with loupe flat against a table and raise as needed to focus.

#### CARE:

Clean using microfiber lens cloth. Do not use any abrasives, chemical cleaners, or solvents.

#### Customer Service:

If you experience any difficulties, please contact us and we will be happy to help you.



✉ info@carson.com



✉ uksupport@carson.com



✉ eusupport@carson.com

For warranty information, visit [www.carson.com/warranty](http://www.carson.com/warranty)

[www.carson.com](http://www.carson.com)

Carson Optical 2070 5th Avenue, Ronkonkoma, NY 11779 | Tel: 631-963-5000